

etolmat ZDS

Automatic admix dosing unit, suitable for foaming a liquid product

Device description

- > Simple and efficient cleaning-in-place system for controlled use of detergents
- > No aerosol formation as in high-pressure cleaning
- > Protects against water refraction and thus against any unintentional spread of bacteria
- > Minimal physical stress for the operator

Delivery/ Connection material

- 1 Jet Neat Foam system 2,5 l
- 1 Jet Neat wall mount
- 1 Rinse attachment
- 15 Dosing nozzles
- 1 Spray hose 15 m
- 2 Screws vertical head 5 x 40
- 2 Plugs S6

Technical data

- > Flowpressure..... Minimum 2 and max. 9 bar, recommended 2-6 bar
- > Concentration..... Adjustable via nozzles
- > Water supply..... G 3/4" male thread
- > Water temperatur..... Max. 50° C

Product image



etolmat ZDS

Spare parts

| <u>Article</u> | <u>Description</u> |
|----------------|----------------------|
| 2000477 | Dosing nozzles |
| 2000480 | Spray hose 15 m |
| 2000761 | Jet Neat Foam System |
| 2000762 | Jet Neat Wall Mount |
| 2000903 | Spray hose 20 m |

etolmat ZDS

Additional info

Principle

When connecting to the home water system, an addition on the injector takes place. There is a low pressure in the suction line for the product by converting the pressure energy into velocity and the subsequent relaxation. The concentration is accurately adjusted by interchangeable metering nozzles.

Guideline

Doyen F 40

| | | |
|---------------|-------|---------------|
| <u>yellow</u> | 0,5 % | 50 ml / 10 l |
| orange | 0,8 % | 80 ml / 10 l |
| <u>blue</u> | 2,0 % | 200 ml / 10 l |
| <u>white</u> | 2,3 % | 230 ml / 10 l |
| red | 3,0 % | 300 ml / 10 l |

Biguanid Fläche N

| | | |
|--------|-------|---------------|
| orange | 1,0 % | 100 ml / 10 l |
|--------|-------|---------------|

etolit All Purpose Cleaner

| | | |
|---------------|-------|---------------|
| aquamarine | 0,5 % | 50 ml / 10 l |
| <u>yellow</u> | 0,7 % | 70 ml / 10 l |
| <u>orange</u> | 1,0 % | 100 ml / 10 l |
| blue | 2,5 % | 250 ml / 10 l |

etolit Degreaser

| | | |
|------------|-------|---------------|
| <u>red</u> | 3,0 % | 300 ml / 10 l |
|------------|-------|---------------|

etolit Basic Cleaner

| | | |
|--------|-------|---------------|
| orange | 1,0 % | 100 ml / 10 l |
|--------|-------|---------------|

The values are dependent on the water pressure and vary from home to home. It is therefore advisable to check the dosage for installation or alteration of the water supply.

Check of the dosage

- pour in the product into a measuring cylinder.
- read off the value.
- fill a 10 liter bucket over the etolmat ZDE.
- read off the consumption of the product.
- summary: product in ml / 10 l